

Rowenta X-Clean 4 , Lavapavimenti Senza Fili con Auto-Propulsione e Rilevazione Automatica dello Sporco, Doppio Serbatoio e Sistema di Autopulizia, Autonomia 50' per Tutti i Tipi di Pavimenti, GZ5035

Marchio : Rowenta

Famiglia del prodotto: X-Clean 4

Codice prodotto: GZ5035WO

Nome del prodotto : Rowenta X-Clean 4, Lavapavimenti Senza Fili con Auto-Propulsione e Rilevazione Automatica dello Sporco, Doppio Serbatoio e Sistema di Autopulizia, Autonomia 50' per Tutti i Tipi di Pavimenti, GZ5035

Rowenta X-Clean 4 , Lavapavimenti Senza Fili con Auto-Propulsione e Rilevazione Automatica dello Sporco, Doppio Serbatoio e Sistema di Autopulizia, Autonomia 50' per Tutti i Tipi di Pavimenti, GZ5035. Tipo di prodotto: Aspirapolvere elettrica, Tipo di contenitore della polvere: Senza sacchetto, Colore del prodotto: Grigio. Tipo di pulizia: Secco e bagnato, Sistema di filtraggio dell'aspirapolvere: Schiuma, Metodo di separazione dello sporco: Filtraggio Aqua. Controllo dell'energia: Elettronico. Alimentazione: Batteria, Massima potenza in entrata: 200 W, Tecnologia batteria: Ioni di Litio. Larghezza imballo: 288 mm, Profondità imballo: 748 mm, Altezza imballo: 327 mm



Design		Power	
Product type *	Stick vacuum	Battery technology	Lithium-Ion (Li-Ion)
Dust container type *	Bagless	Number of batteries supported	1
Product colour *	Grey	Runtime	50 min
Number of water tanks	1	Charging time	4.25 h
Removable water tank	✓	Power plug type	Type C
Brush shape	Rectangular	Packaging data	
Performance		Package width	288 mm
Cleaning type *	Dry&wet	Package depth	748 mm
Vacuum air filtering *	Foam	Package height	327 mm
Dirt separating method *	Aqua filtering	Package weight	7.34 kg
Foam filter	✓	Quantity per pack	1 pc(s)
Cleaning surfaces	Hard floor	Other features	
Built-in display	✓	Removable handheld vacuum	✗
Area cleaned per battery charge	350 m²	Weight & dimensions	
Number of power levels	3	Width	315 mm
Suction power mode	Max, Medium	Depth	305 mm
Display type	LCD	Height	1147 mm
Ergonomics		Weight	5.4 kg
Power control	Electronic	Logistics data	
On/off switch	✓	Products per intermodal container (20ft)	393 pc(s)
Parking position	✓	Products per intermodal container (40ft)	804 pc(s)
Variable power	✓	Products per pallet layer	4 pc(s)
Ergonomic handle	✓	Layers per pallet	7 pc(s)
Power		Products per pallet	28 pc(s)
Power source *	Battery		
Maximum input power *	200 W		



3221616130012

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 24-FEB-2025. Prints or copies of Information are only valid on the printed Publication date